

# SAUTER HDD 100-1

Professional Shore hardness tester

# KERN



## Category

Brand	Sauter
Product category	Hardness testing
Product group	Digital Shore hardness tester
Product family	HD

## Measuring System

Readability hardness [d] (Shore)	0,1
Measuring range Shore	100
Test object thickness [Min]	6 mm
Hardness scales	Shore D
Units	HD
Tolerance (% of [Max])	1%
Test force Hardness measurement	50 N
Measuring probe diameter	18 mm

## Display

Display type	LCD
--------------	-----

## Construction

Dimension (W×D×H)	162×65×38 mm
Dimension housing (W×D×H)	162×65×38 mm
Material housing	plastic
Scale - Display type	Digital

## Functions

Function for averaging	✓
Hold function	✓
Peak function	✓

## Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AAA
Battery capacity	1.300 mAh
Battery voltage	1,5 V
Battery - Number of cells	2
Battery - Individual weight	23 g
Battery - Total weight	46 g
Battery - Construction	Individual cells
Battery capacity (Wh)	1,95 Wh
Battery/Accu connected	not connected, enclosed

## Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	50 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Approval

CE mark	✓
---------	---

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	250×197×52 mm
Shipping method	Parcel service
Net weight approx.	0,20 kg
Gross weight approx.	0,85 kg
Shipping weight	0,82 kg

## Product information

GTIN/EAN number	4045761139596
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION

