

KERN HDD100-1.

Professionelles Shore Härteprüfgerät

KERN[®]



Construction

Casing material:	Plastic
Overall dimensions mounted (WxDxH):	162 x 65 x 38 mm

Measuring system

Measuring range (Max):	100
Precision (of [Max]):	1 %
Readout:	0,100
Weighing units:	Shore D

Functions

Data hold function:	yes
Obtaining average:	yes
Peak function:	yes

Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

Category

Brand:	Sauter
Category:	Hardness testers

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	250 x 210 x 53 mm
Gross weight:	820 g
Net weight:	173 g
Shipping method:	Parcel service