

DimMax 420SLR

- DIN rail universal 230V silent dimmer
- For classical bulbs, halogens from 0 to 420 Watt
- For LED and filament LED lighting systems from 0 to at least 200 Watt
- 4 protection systems against over-current, short cuts and over-temperature
- 2 classical modes: trailing edge, leading edge
- 2 LED modes: power optimized and antiflicker-optimized for filament LED
- All LED lamps types can be fully extinguished (no precharge accessory needed)
- Minimum threshold adjustment
- Low own standby consumption
- Last dimming point can be memorized
- 5 year warranty



Please note the installation- and safety instructions.



	66003001
Product	DimMax 420SLR
IP protection class	IP 20
Connection via	DIN rail
Colour of body	weiß
Ambient temperature	-10~+40 °C
Length	98 mm
Width	57 mm
Height	18 mm
Weight	45 gr