Water Sensor

Product ref.: 151694A0



Technical specifications

Supply voltage	2x 1,5 V LR03/micro/AAA
Current consumption	100 mA max.
Battery life	5 years (typ.)
Degree of protection	IP44
Ambient temperature	-20 to +55 °C
Dimensions (W x H x D)	80 x 80 x 30 mm
Weight	78.2 g (including batteries)
Radio frequency band	868.0-868.6 MHz 869.4-869.65 MHz
Typ. open area RF range	230 m



Product features

- Reliably detects humidity on different surfaces as well as a water level from 1.5 mm height
- Arising humidity and water are indicated via the integrated siren of the water sensor or, if available, via the Homematic IP Alarm Siren as well as the Homematic IP App
- With an integrated tilt sensor, unintended movement or manipulation of the water sensor is detected and indicated immediately
- Flexible adaptation to the installation site thanks to battery operation and spring-mounted measuring probes
- Individual adjustment of triggering behaviour via the Homematic IP app
- For operation, the Homematic IP Access Point in connection with the Homematic IP app (no recurring costs), the Homematic Central Control Unit CCU2 or an appropriate partner solution is required

Logistical data

Product reference	151694A0
EAN code	4047976516940
Short description	HmIP-SWD
Packing unit	90
Packing dimensions	122 x 112 x 48 mm
Weight incl. packaging	154.2 g

Package contents

Homematic IP Water Sensor

1.5 V LR03/micro/AAA batteries (2x)

User manual