

SIVACON, Control panel Empty enclosure, without side panels, according to IEC 62208, IP40, H: 2000 mm, W: 1200 mm, T: 1000 mm



Model	
Product brand name	SIVACON
Product designation	Empty control cabinet enclosure
Design of the product	according to IEC 62208
Design of the surface	Powder-coated
Design of the product / EMC version	No
Protection class	
Protection class IP	IP40
Operating resource protection class	Safety class 1
Suitability	
Suitability for installation / for metric dimensions	Yes
Suitability for integration	
• surface-mounted installation	Yes
• flush mounting	No
Suitability for use / for outside use	No
Appearance	
RAL color number	RAL 7035
Color	light grey

Product details

Product component	
• Ventilation door	No
• Mounting plate	Yes
• Rear door	No
• Viewing door	No
• height-adjustable mounting plate	Yes
Product feature / of the enclosure / housing for side-by-side mounting	Yes

Number

Number of locking devices	0
Number of doors	2

Mechanical Design

Height	2 000 mm
Width	1 200 mm
Depth	1 000 mm
Mounting type	
• 19-inch installation	No
• floor mounting	Yes
• wall mounting	No
Net weight	194.14 kg
Material	steel

Certificates

Reference code	
• acc. to DIN EN 61346-2	U
• acc. to DIN EN 81346-2	UC

General Product Approval	Declaration of Conformity	Test Certificates	other
--------------------------	---------------------------	-------------------	-------



[Special Test Certificate](#)

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1020-3BR4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1020-3BR4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1020-3BR4



