

standard cabinet 8MF2 HxWxD=2200x 600x 800 Installation: Side-by-side ventilated, mounted, welded IP30



Figure similar

| Model                                          |                                                            |
|------------------------------------------------|------------------------------------------------------------|
| Product brand name                             | SIVACON                                                    |
| Product designation                            | standard system cubicle                                    |
| Type of installation                           | installation as suite                                      |
| Design of the surface                          | powder-coated                                              |
| Design of the product / EMC version            | No                                                         |
| Design of the control cabinet / PC design      | No                                                         |
| Design of the control cabinet / Console design | No                                                         |
| Protection class                               |                                                            |
| Protection class IP                            | IP30                                                       |
| Suitability for installation                   | 10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch<br>M8 |
| • for inch dimensions                          |                                                            |
| • for metric dimensions                        |                                                            |
| Suitability for use / for outside use          | No                                                         |
| Appearance                                     |                                                            |
| RAL color number                               | RAL 7032                                                   |
| Color                                          | pebble grey                                                |

|                                    |     |
|------------------------------------|-----|
| Product component                  |     |
| • removable frame                  | No  |
| • Ventilation door                 | Yes |
| • Mounting plate                   | No  |
| • Rear door                        | No  |
| • pitched roof                     | No  |
| • Viewing door                     | No  |
| • height-adjustable mounting plate | No  |
| Number of locking devices          | 1   |
| Number of doors                    | 1   |

## Mechanical Design

|                                                          |          |
|----------------------------------------------------------|----------|
| Height                                                   | 2 200 mm |
| Width                                                    | 600 mm   |
| Depth                                                    | 800 mm   |
| Number of modular height units / for installation height | 43       |
| Mounting type                                            | standing |
| Mounting type / 19-inch installation                     | Yes      |
| Net weight                                               | 145 kg   |
| Material                                                 | steel    |

## Certificates

|                                 |              |
|---------------------------------|--------------|
| Reference code                  |              |
| • acc. to DIN EN 61346-2        | U            |
| <b>General Product Approval</b> | <b>other</b> |

[Miscellaneous](#)



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF2268-3RB>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF2268-3RB>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF2268-3RB](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF2268-3RB)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>