

EMC cabinet IP40 HxWxD=1800x 600x 600 for stand-alone installation with side panels, IP40



Figure similar

Model	
Product brand name	SIVACON
Product designation	EMC cubicle
Type of installation	stand-alone installation
Design of the surface	frames and enclosure parts zinkcor-coated, enclosure parts powder-coated on the outside
Design of the product / EMC version	Yes
Design of the control cabinet / PC design	No
Design of the control cabinet / Console design	No
Protection class	
Protection class IP	IP40
Suitability for installation	<ul style="list-style-type: none"> • for inch dimensions 10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch • for metric dimensions M8
Suitability for use / for outside use	No
Appearance	
RAL color number	RAL 7032

Color	pebble grey
Product component	
<ul style="list-style-type: none"> • removable frame • Ventilation door • Mounting plate • Rear door • pitched roof • Viewing door • height-adjustable mounting plate 	<ul style="list-style-type: none"> No No No No No No No
Number of locking devices	1
Number of doors	1

Mechanical Design	
Height	1 800 mm
Width	600 mm
Depth	600 mm
Number of modular height units / for installation height	34
Mounting type	standing
Mounting type / 19-inch installation	Yes
Net weight	100 kg
Material	steel

Certificates	
Reference code	
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 	U

General Product Approval	other
---------------------------------	-------

[Miscellaneous](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=8MF2866-4ES>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF2866-4ES>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MF2866-4ES

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

