

SENTRON, cylindrical fuse link, 10 x 38 mm, 12 A, aM, Un AC: 500 V



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse link
General technical data	
Operating class of the fuse link	aM
Size of the fuse link	10x38 mm
Type of voltage	AC
Current / at AC / rated value	12 A
Supply voltage / at DC	250 V
Operating voltage / rated value	500 V
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	0.8 W
Main circuit	
Operating current / Rated value	12 A
Product details	
Product component / striker	No
Mounting position	Any, preferably vertical

Net weight

7 g

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

Declaration of Conformity



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW8006-1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW8006-1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW8006-1

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

