

Standard cabinet 8MF5 HxWxD=1800x 800x 800 Installation: Side-by-side non-ventilated, not mounted, screwed IP40



Figure similar

| Model                                          |                                                      |
|------------------------------------------------|------------------------------------------------------|
| Product brand name                             | SIVACON                                              |
| Product designation                            | standard system cubicle                              |
| Type of installation                           | installation as suite                                |
| Design of the surface                          | powder-coated                                        |
| Design of the product / EMC version            | No                                                   |
| Design of the control cabinet / PC design      | No                                                   |
| Design of the control cabinet / Console design | No                                                   |
| Protection class                               |                                                      |
| Protection class IP                            | IP40                                                 |
| Suitability for installation                   |                                                      |
| • for inch dimensions                          | 10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch |
| • for metric dimensions                        | M8                                                   |
| Suitability for use / for outside use          | No                                                   |
| Appearance                                     |                                                      |
| RAL color number                               | RAL 7032                                             |
| Color                                          | pebble grey                                          |

|                                    |    |
|------------------------------------|----|
| Product component                  |    |
| • removable frame                  | No |
| • Ventilation door                 | No |
| • Mounting plate                   | No |
| • Rear door                        | No |
| • pitched roof                     | No |
| • Viewing door                     | No |
| • height-adjustable mounting plate | No |
| Number of locking devices          | 1  |
| Number of doors                    | 1  |

| Mechanical Design                                        |          |
|----------------------------------------------------------|----------|
| Height                                                   | 1 800 mm |
| Width                                                    | 800 mm   |
| Depth                                                    | 800 mm   |
| Number of modular height units / for installation height | 34       |
| Mounting type                                            | standing |
| Mounting type / 19-inch installation                     | Yes      |
| Net weight                                               | 110 kg   |
| Material                                                 | steel    |

| Certificates             |                           |       |
|--------------------------|---------------------------|-------|
| Reference code           |                           |       |
| • acc. to DIN EN 61346-2 | U                         |       |
| General Product Approval | Declaration of Conformity | other |



[Miscellaneous](#)

| Further information                                                                                                                                                                                                                                               |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Information- and Downloadcenter (Catalogs, Brochures,...)</b><br><a href="http://www.siemens.com/lowvoltage/catalogs">http://www.siemens.com/lowvoltage/catalogs</a>                                                                                           |
| <b>Industry Mall (Online ordering system)</b><br><a href="https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF5888-4R">https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF5888-4R</a>                                          |
| <b>Service&amp;Support (Manuals, Certificates, Characteristics, FAQs,...)</b><br><a href="https://support.industry.siemens.com/cs/ww/en/ps/8MF5888-4R">https://support.industry.siemens.com/cs/ww/en/ps/8MF5888-4R</a>                                            |
| <b>Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)</b><br><a href="http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF5888-4R">http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF5888-4R</a> |
| <b>CAX-Online-Generator</b><br><a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>                                                                                                                                                                |
| <b>Tender specifications</b><br><a href="http://www.siemens.com/specifications">http://www.siemens.com/specifications</a>                                                                                                                                         |

