

SIMBOX XL, 2-tier Wall recessed box flush-mounting 2-tier 24 MW
VPE 12 units



Figure similar

Model	
Product brand name	ALPHA
Product designation	SIMBOX XL
Design of the product	1-tier, wall box, HW
Design of support rail	Standard mounting rail 35 mm x 7.5 mm acc. to EN 60715
Design of the cap/top cover	closed
Design of the product / EMC version	No
Supply voltage	
Operating voltage / at AC / rated value	400 V
Protection class	
Protection class IP	IP30
Operating resource protection class	II
Current	
Current / at AC / rated value / maximum	63 A
Appearance	
RAL color number	RAL9010

Color	white
-------	-------

Product details

Product component	
• DIN mounting panel	No
• Mounting plate	No
• transparent cover	No
Product extension / optional / Side-by-side mounting	No

Number

Number of rows	1
----------------	---

Mechanical Design

Height	373.6 mm
Width	340.6 mm
Depth	90 mm
Installation depth	70 mm
Number of width units	12
Mounting type	hollow wall
Opening angle of door	125°
Busbar center-to-center spacing	125 mm
Net weight	821 g
Material / of the enclosure	plastic

Certificates

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GB5224-1KM01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8GB5224-1KM01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GB5224-1KM01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

