

Standard cabinet 8MF5 HxWxD=1800x 900x 800 Installation: single non-ventilated, not mounted, screwed IP54,



Figure similar

| Model                                          |                                                      |
|------------------------------------------------|------------------------------------------------------|
| Product brand name                             | SIVACON                                              |
| Product designation                            | standard system cubicle                              |
| Type of installation                           | stand-alone installation                             |
| Design of the surface                          | powder-coated                                        |
| Design of the product / EMC version            | No                                                   |
| Design of the control cabinet / PC design      | No                                                   |
| Design of the control cabinet / Console design | No                                                   |
| Protection class                               |                                                      |
| Protection class IP                            | IP54                                                 |
| Suitability for installation                   |                                                      |
| • for inch dimensions                          | 10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch |
| • for metric dimensions                        | M8                                                   |
| Suitability for use / for outside use          | No                                                   |
| Appearance                                     |                                                      |
| RAL color number                               | RAL 7032                                             |
| Color                                          | pebble grey                                          |

|                                    |    |
|------------------------------------|----|
| Product component                  |    |
| • removable frame                  | No |
| • Ventilation door                 | No |
| • Mounting plate                   | No |
| • Rear door                        | No |
| • pitched roof                     | No |
| • Viewing door                     | No |
| • height-adjustable mounting plate | No |
| Number of locking devices          | 1  |
| Number of doors                    | 1  |

| Mechanical Design                                        |          |
|----------------------------------------------------------|----------|
| Height                                                   | 1 800 mm |
| Width                                                    | 900 mm   |
| Depth                                                    | 800 mm   |
| Number of modular height units / for installation height | 34       |
| Mounting type                                            | standing |
| Mounting type / 19-inch installation                     | Yes      |
| Net weight                                               | 120 kg   |
| Material                                                 | steel    |

| Certificates                    |                                  |              |
|---------------------------------|----------------------------------|--------------|
| Reference code                  | U                                |              |
| • acc. to DIN EN 61346-2        |                                  |              |
| <b>General Product Approval</b> | <b>Declaration of Conformity</b> | <b>other</b> |



[Miscellaneous](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF5898-5E>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8MF5898-5E>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF5898-5E](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF5898-5E)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

