



PIN OUT

J1	J2
1	1
3	3
2	2
4	4
6	6
5	5
7	7
9	9
8	8
10	10
12	12
11	11
13	13
14	14
15	15
16	16
17	17
18	18
19	19
Shell	Shell

NOTE:

1. Electrical test:

- (1). 100% open short & miss wire test;
- (2). Insulation resistance: DC 200V 10M ohm;
- (3). Contactor resistance: 3 ohm;
- (4). Dielectric strength: 300V AC/Sec, 2mA.

Suppur 4K*2K@60HZ

OPERATING TEMPERATURE: 0°C ~ 45°C

STORAGE TEMPERATURE: -20°C ~ 70°C

RoHS 2.0 And REACH Compliant

Packing: 1pc/polybag+label

MATERIAL LIST:

④	Outer Face plate	ABS 80*80MM White RAL 9003	1	
③	Bracket	SECC T1.2mm	1	
②	Inner Face plate	ABS 50*50MM White RAL 9003	1	
①	HDMI Adapter	HDMI A Female/Female 180 degree, PIN Gold plating, Shell Gold plating	1	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
		NEW		2018-06-01 A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV. Alvan Alvan

CUSTOMER		ITEM NO.	29212c177		
PRODUCT NAME	HDMI 2.0a AF-AF Adapter with Faceplate Germany Type	UNO ITEM NO.	255181	UNIT	MM
		APPOBY	DATE		
			2018-06-01		