

Datenblatt

Impedance	50 Ω
Frequency range	0-3 GHz
VSWR (straight connectors)	≤ 1.22 typ
Insulation resistance	≥ 5 x 10 ³ MΩ
Center contact resistance	≤ 10.0 mΩ
Outer contact resistance	≤ 5.0 mΩ
Test voltage	1000V rms
Working voltage	500 V rms
Insertion loss(dB)	≤ 0.1dB max/1GHz typ

NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER J15-C3604
2. TEFLON MIL-P-19468
3. NICKEL PL 70 μ" THICK PLATING
4. GOLD PL 1-3μ" OVER NICKEL PL 70 μ" THICK PLATING

No	Description	Material	Finish
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel

