

Type.....	57971
Designation.....	Power Bank 13000 mAh
Systems to charge.....	Li-Ion
Cell configurations.....	Li-Ion 18650, 5 pcs. 2600 mAh
Housing Material:.....	ABS
Casing colour:.....	Depending on PO
Dimensions:	Charger:
Length.....	140 +-1 mm
Width.....	79.5 +-1 mm
Height.....	22 +-1 mm
Weight.....	310 +-5 g



Charging methods:

Li-Ion

Plug in Micro USB port:

Current: 500 – 2000 mA

Maintenance Charge:

N/A

Discharging methods:

Output:

USB port for charging other devices:

5.0 V 1000 mA and 2400 mA
(max 2400 mA total output)

Indications for IN:



Indications for OUT:



Flashlight: Press button for 1s to enable LED

Power IN: Primary: 5 V DC 1000 mA
Secondary: 3.7 V DC

Power OUT: Primary: 3.7 V DC
Secondary: 5 V DC 1000 mA and 2400 mA

Cut off criteria:

Li-Ion cells: Stop discharging, when Li-Ion voltage lower than 2.8 V
Short circuit protection
Overload protection

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries