

Type..... 57972
Designation..... Power Bank 18200 mAh
Systems to charge..... Li-Ion
Cell configurations..... Li-Ion 18650, 7 pcs. 2600 mAh
Housing Material..... ABS
Casing colour..... Depending on PO

Dimensions:
Length..... 160 +-1 mm
Width..... 82 +-1 mm
Height..... 22 +-1 mm
Weight..... 414 +-5 g

Charger:
 160 +-1 mm
 82 +-1 mm
 22 +-1 mm
 414 +-5 g



Charging methods:
Li-Ion

Plug in Micro USB port:
Current: 500 – 2000 mA

Maintenance Charge:
N/A

Discharging methods:
Output:

USB port for charging other devices:
5.0 V 1000 mA and 2400 mA
(max 2400 mA total output)

Indications for IN:



Indications for OUT:



Flashlight: Press button for 1s to enable LED

Power IN: Primary: 5 V DC 1000 mA
 Secondary: 3.7 V DC

Power OUT: Primary: 3.7 V DC
 Secondary: 5 V DC 1000 mA and 2400 mA

Cut off criteria:

Li-Ion cells: Stop discharging, when Li-Ion voltage lower than 2.8 V
 Short circuit protection
 Overload protection

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries