

**Connecting elements**  
**H35,0/30S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For conductors from 10.0 to 185.0 mm<sup>2</sup> (AWG 7 - 350 MCM)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1  
• supplied loose in poly-bag

**General ordering data**

Type	H35,0/30S
Order No.	<a href="#">945100000</a>
Version	Wire-end ferrule, uninsulated, 30 mm
GTIN (EAN)	4008190071516
Qty.	100 pc(s).
Packaging	loose

**Data sheet**

**Connecting elements  
H35,0/30S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	30 mm	Width (inches)	1.181 inch
Net weight	1.49 g		

**Technical data**

Version	uninsulated
---------	-------------

**Wire-end ferrules**

Collar diameter (D2)	11 mm	Conductor cross-section	35 mm <sup>2</sup>
Contact surface diameter (D1)	8.3 mm	L1 in mm	30 mm
Stripping length	30 mm	Wire connection cross section AWG, max.	AWG 2

**Classifications**

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements  
H35,0/30S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

**Similar to illustration**

