
# KERN **KIB-A06**

Signal lamp, including interface, for visual support of weighing with tolerance range



## Product information

| | |
|---|---|
| GTIN/EAN number | 4045761207066 |
| REACH classification | no prohibited substances |

## Pictograms

**STANDARD**




## Category

| | |
|---|---|
| Brand | KERN |
| Product categoriy | Balance |
| Product group | Signal lamp |

## Measuring System

| | |
|---|---|
| Linearity | ± |

## Construction

| | |
|---|---|
| Dimension (W×D×H) | 100×180×300 mm |

## Functions

| | |
|---|---|
| IP protection - complete device | - |

## Environmental conditions

| | |
|---|---|
| Ambient temperature [Min] | -20 °C |
| Ambient temperature [Max] | 60 °C |
| Storage temperature [Min] | -20 °C |
| Storage temperature [Max] | 60 °C |

## Approval

| | |
|---|---|
| CE mark | ✓ |

## Packing & Shipping

| | |
|---|---|
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 260×650×155 mm |
| Shipping method | Parcel service |
| Net weight approx. | 1,2 kg |
| Gross weight approx. | 1,8 kg |
| Shipping weight | 5,2 kg |