

SR60 base DIAZED DII 3-pole 500 V AC DC for adaptor screw for 5/10 mm busbar thickness with clamp-type terminals



Figure similar

Model	
Product brand name	SENTRON
Product designation	DIAZED fuse system
Design of the product	SR60 BASE
Design of the fuse base	gauge inset
General technical data	
Number of poles	3
Size of fuse system / acc. to DIN EN 60269-1	DII
Supply voltage	
Current / at AC / rated value	25 A
Supply voltage / at AC / rated value	500 V
Product details	
Product component / Cover	No
Mechanical Design	
Height	200 mm
Width	42 mm

Depth	43.5 mm
Net weight	226 g
Material / of the enclosure	others

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

Test Certificates

[Type Test Certificates/Test Report](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SF6015>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SF6015>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF6015

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

