

MLFB-Ordering data

6SL3203-0CD21-0AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
<b>Input</b>		<b>Line side</b>	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	380 ... 480 V	<b>Load side</b>	
<b>Output</b>		Version	Cable
Rated current	9.0 A	Conductor cross-section	1.50 mm <sup>2</sup> (16 AWG)
<b>Mechanical data</b>		Cable length	0.46 m (1.51 ft)
<b>Dimensions</b>		<b>PE connection</b>	
Width	153.0 mm (6.0 in)	Version	M5 screw studs
Height	270.0 mm (10.6 in)	<b>Standards</b>	
Depth	70.0 mm (2.8 in)	Compliance with standards	cURus
Degree of protection	IP20 / UL open type		
Net weight	3.4 kg (7.5 lb)		