

SENTRON, cylindrical fuse holder, 10x38 mm, 3-pole, In: 32 A, Un AC: 690 V, for busbar system 8US 60 mm



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse holder
Design of the product	For 60 mm 8US busbar system
General technical data	
Number of poles	3
Size of fuse link	10 x 38 mm
Supply voltage	
Current / at AC / rated value	32 A
Operating voltage	690 V
• at AC / rated value	
Protection class IP	IP20
Mechanical Design	
Height	200 mm
Width	27 mm
Depth	79 mm
Certificates	

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F  
F

General Product Approval

Declaration of Conformity



Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3NW7431>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7431>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW7431](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW7431)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





