

Data sheet for Line reactor

MLFB-Ordering data

6SE6400-3CC02-6BB3



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Input		Line side	
Number of phases	1 AC	Version	screw-type terminal
Line voltage	200 ... 240 V	Conductor cross-section	1.50 ... 6.00 mm ² (16 ... 10 AWG)
Output		Load side	
Rated current	22.8 A	Version	Pigtail
Mechanical data		Conductor cross-section	2.50 mm ² (14 AWG)
Dimensions		Cable length	0.46 m (1.51 ft)
Width	150.0 mm (5.9 in)	PE connection	
Height	213.0 mm (8.4 in)	Version	M5 stud
Depth	50.0 mm (2.0 in)	Standards	
Degree of protection	IP20 / UL open type	Compliance with standards	cURus
Net weight	2.2 kg (4.8 lb)		