

MLFB-Ordering data

6SL3501-0BE12-1AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Rated power P_{db} 0.200 kW

Rated power, max. 4.00 kW

General tech. specifications

Resistance 160 Ω

Mechanical data

Degree of protection IP65

Net weight 4.50 kg (9.92 lb)

Width 465.0 mm (18.31 in)

Height 199.0 mm (7.83 in)

Depth 120.0 mm (4.72 in)