



Figure similar

MLFB-Ordering data

6SL3201-0BE21-8AA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Rated power P_{db} 0.375 kW

Rated power, max. 7.50 kW

General tech. specifications

Resistance 75 Ω

Mechanical data

Degree of protection IP20 / UL open type

Net weight 2.73 kg (6.02 lb)

Width 175.0 mm (6.89 in)

Height 345.0 mm (13.58 in)

Depth 100.0 mm (3.94 in)

Connections

Power connection

Version Terminal block

Conductor cross-section 2.50 mm²

PE connection

Version Yes

Version on housing M4 screw

Thermostatic switch

Version Normally closed contact

Conductor cross-section 2.50 mm²