

Data sheet for Line reactor

MLFB-Ordering data

6SL3203-0CD25-3AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Input		Line side	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	380 ... 480 V		
Output		Load side	
Rated current	63.0 A	Version	Cable
Mechanical data		Conductor cross-section	16.00 mm ² (6 AWG)
Dimensions		Cable length	0.70 m (2.30 ft)
Width	275.0 mm (10.8 in)	PE connection	
Height	455.0 mm (17.9 in)	Version	M8 Screw
Depth	84.0 mm (3.3 in)	Standards	
Degree of protection	IP20 / UL open type	Compliance with standards	cURus
Net weight	13.0 kg (28.7 lb)		