

USB Charging Adaptor, 2 Port



Manual 31813

Basic Parameter

Weight	65g
Dimension	45*26*89mm
Input	100-240VAC
	50/60Hz
Output	5V4A in total Type-C™ 5V/3A Max USB Port 5V/2.4A Max
Operating Temp.	-10-35°C
Certification	CE

Charging method

- 1. Connect the plug into a socket with 100-240V. The ednet USB wall charger (31813) is ready for use.
- 2. There are USB C and USB A output on the charger to plug in a charging cable. It will provide DC power up to 5V/4A; can charge 2 devices in same time.

Compatibility

It is compatibility to iPad®/iPhone®, Android smartphones/tablets, or any other smartphones/tablet PCs, portable speakers, cameras, etc.

Package Content

- 1 x Main unit
- 1 x User manual

^{*} All brand names and logos which mentioned above are trademarks or registered trademarks of the respective owner.

Maintain

To extend the product life cycle, please do as following:

- Keep it dry and away from damp and erosive goods.
- Don't disassemble the product.
- Don't store it under over-hot or over-cold environment.
- Don't knock or crash the product.

All of the products have been tested and verified. If it occurs over-hot, out of shape, breakage or other abnormal cases, please stop to use and contact with sales agent or our company.

Symbols used: Indoor use only



Hereby Assmann Electronic GmbH, declares that the Declaration of Conformity is part of the shipping content. If the Declaration of Conformity is missing, you can request it by post under the below mentioned manufacturer address.

www.assmann.com

Assmann Electronic GmbH Auf dem Schüffel 3 58513 Lüdenscheid Germany

