

Item no.: BN 1713197

## Data Sheet

---

**FN 960148c01**

BN 1713197

**RE: TOOLCRAFT Digital microscope 20X ~ 200X 2.0MP**

Item photo:



### Technical data:

Operating voltage.....	5 V/DC, 1 A (via USB 2.0)
Connection.....	USB 2.0 (Type A)
Image sensor.....	2 MP (optical)
Video / still resolution.....	1920x1080, 1280x720, 640x480
Frame Rate : .....	30f/s Under 500 LUX Brightness
Colour depth.....	24 bits RGB
Focus range.....	0 to 150 mm (manual focus)
Magnification ratio.....	20x to 200x
Image format.....	JPG
Video format.....	AVI
White balance.....	Automatic
Supported operating systems.....	Windows® 7/8/10 or above, Mac OS 10.12 or above
Operating conditions.....	0 to +70 °C; 25 - 50 % relative humidity (non-condensing)
Storage conditions.....	-5 to +50 °C; 25 - 50 % relative humidity (non-condensing)
Dimensions Microscope (Ø x L).....	33 x 110 mm
Weight.....	350 g