



**Phase busbar, 2-phases, 10qmm, fork connector, 12SU**

**Part no. EVG-2PHAS/12MODUL**  
**Catalog No. 215641**

**EL-Nummer (Norway) 1657153**

Similar to illustration

## Delivery program

Basic function		Busbar
Basic function accessories		Busbar for miniature circuit-breaker Busbar for residual-current circuit-breakers Busbar for combined residual-current/power circuit-breaker
Busbar type		2 phase
Product range		EVG

## Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ecl@ss10.0.1-27-37-13-06 [ACN992011])		
Number of phases		2
Number of poles		2
Suitable for number of devices		6
Pitch dimensions	mm	0
Cross section	mm <sup>2</sup>	10
Length	mm	210
Number of modular spacings		12
Rated permanent current I <sub>u</sub>	A	63
Type of electric connection		Fork
Insulated		Yes
Rated surge voltage	kV	4
Conditioned rated short-circuit current I <sub>q</sub>	kA	25
Max. rated operation voltage U <sub>e</sub>	V	500
Rated short-time withstand current I <sub>cw</sub>	kA	0
Suitable for devices with N-busbar		No
Suitable for devices with auxiliary switch		No