



NOTE:

1. Electrical test:
 - (1). 100% open short & miss wire test;
 - (2). Insulation resistance: DC 200V 10M ohm min;
 - (3). Contactor resistance: 5 ohm max;
 - (4). Displayport practical application Test Pass 4k*2k@60HZ
3. ROHS 2.0 AND REACH COMPLIANT
4. PRINT WORD: DisplayPort Cable E***** 兄 AWM STYLE 20276 80°C 30V VW-1
5. Operation temperature: -10°C ~ +60°C
 Storage temperature: -20°C ~ +75°C
 Operation humidity: 10% ~ 85%
 Storage humidity: 10% ~ 85%
6. PACKING: 1PCS/Renkfroce giftbox
7. DP1.2 version

⑥	FERRITE	OUTER MOLD BLACK PVC OD14.2* 9*L28.5MM	1	
⑤	TUBE END	BLACK PVC 45P	2	
④	INNER COVER	LD PE	2	
③	OUTER COVER	DP 20PIN MALE BLACK ABS ASSEMBLY TYPE	2	
②	CONNECTOR	DP 20P/M WITH LATCHING SOLDER TYPE, BLACK INSULATION, THE PIN GOLD PLATED, THE SHELL FOR GOLD PLATED	2	
①	CABEL	(28AWG BC*1P+D+AL+MYLAR)*5+28AWG BC*4C+ADB OD7.3±0.2mm, PVC black	1	

File No.	Bestell No.	UNO ITEM No.	LENGTH	Packing
29212c53	1409674	791110.50	500+100/-0	105 x 140mm (depth: 20mm)
29212c52	1404067	791110.81	1800+100/-0	105 x 240mm (depth: 35mm)
29212c54	1404068	791110.03	3000+100/-0	105 x 240mm (depth: 35mm)
29212c55	1404069	791110.05	4500+100/-0	105 x 290mm (depth: 50mm)
	1716996	791110.11	1000+100/-0	105 x 240mm (depth: 35mm)
	1716997	791113,07	7500+100/-0	230x 290mm (depth: 70mm)

NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT'Y	REMARK
	Alvan	Alvan	Add NEW ITEM NO.	2018.08.01 A3
	Alei	Alvan	change the distance of FERRITE to the end of the line to 50	2018.01.18 A2
			Revise Outer mold of ferrite	2017.06.08 A1
			NEW	2016.01.08 A
BY	CHK	REVISION RECORD MODIFICATIONS		DATE REV.

CUSTOMER	CN	ITEM NO.	see the chart	
PRODUCT NAME	DisplayPort 20P Male-Male with clip	UNO ITEM NO.	UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE	
Alei	Alvan		2018.08.01	