

DISCHARGE REACTOR; UN(V):690; I_{EFF}(A):0,02



Figure similar

General technical data:		
Product designation		discharging reactor
Phase number		3
Type of voltage		AC
Operating voltage rated value		
• maximum	V	690
Operating frequency rated value		
• maximum	Hz	0
Current		
• at AC		
— maximum	A	0.02
Mechanical data:		
Type of electrical connection for main current circuit		screw-type terminals
Width	m	0.045
Height	m	0.09
Depth	m	0.06

Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature rated value	°C	40
Protection class IP		IP00

Certificates/ approvals:

General Product Approval	other
--------------------------	-------

[Confirmation](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EJ9900-0EG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EJ9900-0EG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EJ9900-0EG&lang=en

last modified:

09/13/2019