



COMMUTATING CHOKE FOR CONVERTER;  
 PHASES:3; UN1(V):500; ITHMAX 1(A) / F1(HZ):355  
 /50; I LN (A):319,5; UK(%):4; LN(MH):0,0778;  
 TA/ISOKL:40 /H; IP00; TYPE OF TERMINALS:FLAT-  
 TYPE TERMINAL; EN 61558-2-20 >CHOKE<

Figure similar

General technical data:		
Product designation		Kommut.-Drossel f. Stromrichter
Phase number		3
Type of voltage		AC
Operating voltage rated value	V	500
Operating frequency rated value	Hz	50
Current		
• at AC		
— rated value	A	319.5
— maximum	A	355
• at DC rated value	A	435
Peak current	A	444
Inductivity rated value	H	0.000077
Relative inductive drop in voltage on the measurement level current, voltage and frequency	%	4
Power loss [W] of the coil	W	220
Power loss [W] of the iron core	W	117

#### Mechanical data:

Type of electrical connection for main current circuit		flat connector
Width	m	0.3
Height	m	0.269
Depth	m	0.211

#### Ambient conditions:

Thermal class acc. to IEC 60085		H
Ambient temperature rated value	°C	40
Protection class IP		IP00

#### Certificates/ approvals:

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------



[Confirmation](#)

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EU3022-7BA00-0AA0>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EU3022-7BA00-0AA0>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4EU3022-7BA00-0AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EU3022-7BA00-0AA0&lang=en)

last modified:

09/13/2019