

MLFB-Ordering data

6SL3202-0AE16-1CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

<b>Rated data</b>	<b>Connections</b>
-------------------	--------------------

<b>Rated voltage</b>	380.00 ... 480.00 V
<b>Rated current</b>	6.10 A
<b>Power loss</b>	0.090 kW

<b>Mechanical data</b>
------------------------

<b>Width</b>	207.0 mm (8.15 in)
<b>Height</b>	175.0 mm (6.89 in)
<b>Depth</b>	72.5 mm (2.85 in)
<b>Degree of protection</b>	IP20 / UL open type
<b>Net weight</b>	3.40 kg (7.50 lb)

<b>Power connection motor</b>	
-------------------------------	--

<b>Version</b>	screw terminals
<b>Conductor cross-section</b>	4.00 mm <sup>2</sup>

<b>PE connection</b>	
----------------------	--

<b>Version</b>	M4 screw studs
----------------	----------------