

MLFB-Ordering data

6SL3202-0AE20-3SA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases	3 AC	<b>Power connection Power Module</b>	
Line voltage	380 ... 480 V	Version	cable
Rated current	3.5 A	Conductor cross-section	6.00 mm <sup>2</sup>
Power loss	0.027 kW	<b>Power connection motor</b>	
<b>Mechanical data</b>		Version	Cable
Degree of protection	IP20 / UL open type	Conductor cross-section	6.00 mm <sup>2</sup>
Net weight	2.60 kg	<b>Max. motor cable length</b>	
Width	75.5 mm	Shielded	200 m
Height	200.0 mm	Unshielded	300 m
Depth	110.0 mm	<b>PE connection</b>	
		Version	M5 screw studs