

MLFB-Ordering data

6SL3202-0AE21-0CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Rated voltage	380.00 ... 480.00 V	Power connection Power Module	
Rated current	9.40 A	Version	cable
Power loss	0.020 kW	Conductor cross-section	1.50 mm ²
Mechanical data		Length	0.40 m
		Power connection motor	
		Version	screw terminals
		Conductor cross-section	6.00 mm ²
		Max. motor cable length	
Width		3 AC 380 V -10 % ... 400 V	
		Shielded	150 m
Height		3 AC 401 V ... 480 V +10 %	
		Unshielded	225 m
Depth		Shielded	
		100 m	
Degree of protection		Unshielded	
		150 m	
Net weight		PE connection	
		Version	M5 screw studs