

MLFB-Ordering data

6SL3202-0AE21-4SA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases	3 AC	Power connection Power Module	
Line voltage	380 ... 480 V	Version	cable
Rated current	14.0 A	Conductor cross-section	6.00 mm ²
Power loss	0.085 kW	Power connection motor	
Mechanical data		Version	Cable
Degree of protection	IP20 / UL open type	Conductor cross-section	6.00 mm ²
Net weight	10.00 kg	Max. motor cable length	
Width	153.0 mm	Shielded	200 m
Height	270.0 mm	Unshielded	300 m
Depth	100.0 mm	PE connection	
		Version	M5 screw studs