

MLFB-Ordering data

6SL3202-0AE23-3SA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases	3 AC	<b>Power connection Power Module</b>	
Line voltage	380 ... 480 V	Version	cable
Rated current	33.0 A	Conductor cross-section	10.00 mm <sup>2</sup>
Power loss	0.151 kW	<b>Power connection motor</b>	
<b>Mechanical data</b>		Version	Cable
Degree of protection	IP20 / UL open type	Conductor cross-section	6.00 mm <sup>2</sup>
Net weight	23.00 kg	<b>Max. motor cable length</b>	
Width	189.0 mm	Shielded	200 m
Height	336.0 mm	Unshielded	300 m
Depth	140.0 mm	<b>PE connection</b>	
		Version	M5 screw studs