

MLFB-Ordering data

6SL3202-0AE23-8CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data	Connections
------------	-------------

Rated voltage	380.00 ... 480.00 V
Rated current	39.00 A
Power loss	0.110 kW

Mechanical data

Width	257.0 mm (10.12 in)
Height	235.0 mm (9.25 in)
Depth	114.7 mm (4.52 in)
Degree of protection	IP20 / UL open type
Net weight	11.20 kg (24.69 lb)

Power connection motor

Version	screw terminals
Conductor cross-section	16.00 mm ²

PE connection

Version	M5 screw studs
---------	----------------