

MLFB-Ordering data

6SL3202-0AJ23-2CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Rated voltage	380.00 ... 480.00 V	Power connection Power Module	
Rated current	32.00 A	Version	cable
Power loss	0.060 kW	Conductor cross-section	1.50 mm ²
Mechanical data		Length	0.35 m
Width	189.0 mm (7.44 in)	Power connection motor	
Height	334.0 mm (13.15 in)	Version	screw terminals
Depth	80.0 mm (3.15 in)	Conductor cross-section	6.00 mm ²
Degree of protection	IP00	Max. motor cable length	
Net weight	9.10 kg (20.06 lb)	3 AC 380 V -10 % ... 400 V	
		Shielded	150 m
		Unshielded	225 m
		3 AC 401 V ... 480 V +10 %	
		Shielded	100 m
		Unshielded	150 m
		PE connection	
		Version	M5 screw studs