

MLFB-Ordering data

6SL3203-0BE21-8BA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Input

Number of phases	3 AC
Line voltage	380 ... 480 V

Output

Rated current	23.5 A
---------------	--------

Mechanical data

Dimensions

Width	100.0 mm
Height	297.0 mm
Depth	85.0 mm
Degree of protection	IP20 / UL open type
Net weight	4.0 kg

Connections

Line side

Version	screw-type terminal
Conductor cross-section	2,5 ... 6,0 mm ²

Load side

Version	shielded lead
Conductor cross-section	4.00 mm ²
Cable length	0.50 m

PE connection

Version	On housing with M5 screw studs
---------	--------------------------------