

MLFB-Ordering data

6SL3203-0BE23-8BA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data	Connections
------------	-------------

Input	
Number of phases	3 AC
Line voltage	380 ... 480 V

Output	
Rated current	49.4 A

Line side	
Version	screw-type terminal
Conductor cross-section	6,0 ... 16,0 mm ²

Load side	
Version	shielded lead
Conductor cross-section	10.00 mm ²
Cable length	0.54 m

Mechanical data

Dimensions	
Width	140.0 mm
Height	359.0 mm
Depth	95.0 mm
Degree of protection	IP20 / UL open type
Net weight	7.3 kg

PE connection	
Version	On housing with M6 screw studs