

MLFB-Ordering data

6SL3203-0CD23-5AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
<b>Input</b>		<b>Line side</b>	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	380 ... 480 V		
<b>Output</b>		<b>Load side</b>	
Rated current	33.0 A	Version	Cable
<b>Mechanical data</b>		Conductor cross-section	2.50 mm <sup>2</sup> (14 AWG)
<b>Dimensions</b>		Cable length	0.49 m (1.61 ft)
Width	189.0 mm (7.4 in)	<b>PE connection</b>	
Height	336.0 mm (13.2 in)	Version	M5 screw studs
Depth	50.0 mm (2.0 in)	<b>Standards</b>	
Degree of protection	IP20 / UL open type	Compliance with standards	cURus
Net weight	6.4 kg (14.1 lb)		