

MLFB-Ordering data

6SL3203-0CE21-8AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
<b>Input</b>		<b>Line side</b>	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	380 ... 480 V		
<b>Output</b>		<b>Load side</b>	
Rated current	22.3 A	Version	screw terminals
<b>Mechanical data</b>		Conductor cross-section	10.00 mm <sup>2</sup> (8 AWG)
<b>Dimensions</b>		<b>PE connection</b>	
Width	125.0 mm (4.9 in)	Version	M5 x 10, washer, spring lock washer
Height	145.0 mm (5.7 in)		
Depth	91.0 mm (3.6 in)	<b>Standards</b>	
Degree of protection	IP20 / UL open type	Compliance with standards	cURus
Net weight	3.0 kg (6.5 lb)		