

MLFB-Ordering data

6SL3203-0CE23-8AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

| Rated data           |                     | Connections               |                                     |
|----------------------|---------------------|---------------------------|-------------------------------------|
| <b>Input</b>         |                     | <b>Line side</b>          |                                     |
| Number of phases     | 3 AC                | Version                   | screw-type terminal                 |
| Line voltage         | 380 ... 480 V       | <b>Load side</b>          |                                     |
| <b>Output</b>        |                     | Version                   | screw terminals                     |
| Rated current        | 47.0 A              | Conductor cross-section   | 16.00 mm <sup>2</sup> (6 AWG)       |
| Mechanical data      |                     | <b>PE connection</b>      |                                     |
| <b>Dimensions</b>    |                     | Version                   | M5 x 10, washer, spring lock washer |
| Width                | 190.0 mm (7.5 in)   | <b>Standards</b>          |                                     |
| Height               | 220.0 mm (8.7 in)   | Compliance with standards | cURus                               |
| Depth                | 91.0 mm (3.6 in)    |                           |                                     |
| Degree of protection | IP20 / UL open type |                           |                                     |
| Net weight           | 7.8 kg (17.2 lb)    |                           |                                     |