

## Data sheet for Line reactor

MLFB-Ordering data

6SL3203-0CJ28-6AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
<b>Input</b>		<b>Line side</b>	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	380 ... 480 V		
<b>Output</b>		<b>Load side</b>	
Rated current	95.0 A	Version	Cable
<b>Mechanical data</b>		Conductor cross-section	35.00 mm <sup>2</sup> (2 AWG)
<b>Dimensions</b>		Cable length	0.70 m (2.30 ft)
Width	275.0 mm (10.8 in)	<b>PE connection</b>	
Height	577.0 mm (22.7 in)	Version	M8 Screw
Depth	94.0 mm (3.7 in)	<b>Standards</b>	
Degree of protection	IP20 / UL open type	Compliance with standards	cURus
Net weight	19.0 kg (41.9 lb)		