

SENTRON, cylindrical fuse holder, 10 x 38 mm, 2-pole, In: 30 A, Ue DC: 1000 V, for photovoltaic application



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse holder
Design of the product	For photovoltaic applications
General technical data	
Number of poles	2
Size of fuse link	10 x 38 mm
Supply voltage	
Current / at AC / rated value	30 A
Operating voltage	
• at DC / rated value	1 000 V
Protection class IP	IP20
Mechanical Design	
Height	85 mm
Width	36 mm
Depth	65 mm
Net weight	122 g

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval

Declaration of Conformity

other



CCC



CSA



UL



EG-Konf.

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7023-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7023-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7023-4

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

