

SETRON, cylindrical fuse holder, 10x38 mm, 2-pole, In: 32 A, Un AC: 690 V, LED signal detector



Model	
Product brand name	SETRON
Product designation	Cylindrical fuse holder
Design of the product	LED signal detector
General technical data	
Number of poles	2
Size of fuse link	10 x 38 mm
Supply voltage	
Current / at AC / rated value	32 A
Operating voltage	690 V
• at AC / rated value	
Protection class IP	IP20
Mechanical Design	
Height	81 mm
Width	36 mm
Depth	64 mm
Net weight	136 g

Certificates

Reference code

- | | |
|--------------------------|---|
| • acc. to DIN EN 61346-2 | F |
| • acc. to DIN EN 81346-2 | F |

General Product Approval

Declaration of Conformity



UR



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7024>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7024>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7024

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





