

SENTRON, cylindrical fuse holder, 8x32 mm, 3-pole, In: 20 A, Un AC: 400 V



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse holder
General technical data	
Number of poles	3
Size of fuse link	8x32 mm
Supply voltage	
Current / at AC / rated value	20 A
Operating voltage	400 V
• at AC / rated value	
Protection class IP	IP20
Mechanical Design	
Height	81 mm
Width	54 mm
Depth	64 mm
Net weight	194 g
Certificates	

#### Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

#### Declaration of Conformity



EG-Konf.

#### Further information

##### **Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

##### **Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7333>

##### **Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7333>

##### **Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7333](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7333)

##### **CAX-Online-Generator**

<http://www.siemens.com/cax>

##### **Tender specifications**

<http://www.siemens.com/specifications>





