

SENTRON, cylindrical fuse holder, 8x32 mm, 1P+N, In: 20 A, Un AC: 400 V, LED signal detector



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse holder
Design of the product	LED signal detector
General technical data	
Number of poles	2
Number of poles / Note	1P+N
Size of fuse link	8x32 mm
Supply voltage	
Current / at AC / rated value	20 A
Operating voltage	400 V
• at AC / rated value	
Protection class IP	IP20
Mechanical Design	
Height	81 mm
Width	18 mm
Depth	64 mm
Net weight	92 g

## Certificates

### Reference code

- |                          |   |
|--------------------------|---|
| • acc. to DIN EN 61346-2 | F |
| • acc. to DIN EN 81346-2 | F |

## Declaration of Conformity



EG-Konf.

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3NW7354>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7354>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW7354](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW7354)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>





