

Data sheet for Line reactor

MLFB-Ordering data

6SE6400-3CC00-2AD3



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Input

Number of phases	3 AC
Line voltage	200 ... 480 V

Output

Rated current	1.9 A
---------------	-------

Mechanical data

Dimensions

Width	75.5 mm (3.0 in)
Height	200.0 mm (7.9 in)
Depth	50.0 mm (2.0 in)
Degree of protection	IP20 / UL open type
Net weight	1.3 kg (2.9 lb)

Connections

Line side

Version	screw-type terminal
Conductor cross-section	1.00 ... 2.50 mm ² (18 ... 14 AWG)

Load side

Version	Pigtail
Conductor cross-section	1.50 mm ² (16 AWG)
Cable length	0.37 m (1.21 ft)

PE connection

Version	M5 stud
---------	---------

Standards

Compliance with standards	cURus
---------------------------	-------