

Data sheet for Line reactor

MLFB-Ordering data

6SE6400-3CC03-5CB3



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Input		Line side	
Number of phases	1 AC	Version	screw-type terminal
Line voltage	200 ... 240 V	Conductor cross-section	2.50 ... 10.00 mm ² (14 ... 8 AWG)
Output		Load side	
Rated current	29.5 A	Version	Pigtail
Mechanical data		Conductor cross-section	8.00 mm ² (10 AWG)
Dimensions		Cable length	0.49 m (1.61 ft)
Width	185.0 mm (7.3 in)	PE connection	
Height	245.0 mm (9.7 in)	Version	M5 stud
Depth	50.0 mm (2.0 in)	Standards	
Degree of protection	IP20 / UL open type	Compliance with standards	cURus
Net weight	3.0 kg (6.7 lb)		