

MLFB-Ordering data

6SE6400-3TC00-4AD2



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Rated voltage	380.00 ... 480.00 V	Power connection Power Module	
Rated current	4.00 A	Version	Pigtail
Power loss	0.005 kW	Length	0.35 m
Mechanical data		Power connection motor	
Width	75.5 mm (2.97 in)	Version	screw terminals
Height	200.0 mm (7.87 in)	Conductor cross-section	2.50 mm ²
Depth	110.0 mm (4.33 in)	Max. motor cable length	
Degree of protection	IP20 / UL open type	3 AC 380 V -10 % ... 400 V	
Net weight	1.90 kg (4.19 lb)	Shielded	150 m
		Unshielded	225 m
		3 AC 401 V ... 480 V +10 %	
		Shielded	100 m
		Unshielded	150 m
		PE connection	
		Version	M5 stud